



Use of Biomass as a Sustainable and Green Fuel with Alkali-Resistant DeNOx Catalysts based on Sulfated or Tungstated Zirconia

Due-Hansen, Johannes; Rasmussen, Søren Birk; Fehrmann, Rasmus; Christensen, Claus H.; Kustov, Arkadii

Publication date:
2006

Document Version
Publisher's PDF, also known as Version of record

[Link back to DTU Orbit](#)

Citation (APA):
Due-Hansen, J., Rasmussen, S. B. (Ed.), Fehrmann, R., Christensen, C. H., & Kustov, A. (2006). *Use of Biomass as a Sustainable and Green Fuel with Alkali-Resistant DeNOx Catalysts based on Sulfated or Tungstated Zirconia*. Poster session presented at 1st International IUPAC Conference on Green-Sustainable Chemistry, Dresden, Germany.

General rights

Copyright and moral rights for the publications made accessible in the public portal are retained by the authors and/or other copyright owners and it is a condition of accessing publications that users recognise and abide by the legal requirements associated with these rights.

- Users may download and print one copy of any publication from the public portal for the purpose of private study or research.
- You may not further distribute the material or use it for any profit-making activity or commercial gain
- You may freely distribute the URL identifying the publication in the public portal

If you believe that this document breaches copyright please contact us providing details, and we will remove access to the work immediately and investigate your claim.

Use of Biomass as a Sustainable and Green Fuel with Alkali-Resistant DeNO_x Catalysts Based on Sulfated or Tungstated Zirconia

Due-Hansen J., Rasmussen S.B., Fehrmann R., Kustov A. L. and Christensen C.H.
 Center for Sustainable and Green Chemistry, Department of Chemistry, Building 206,
 Technical University of Denmark, DK-2800 Lyngby, Denmark



1 Introduction

The use of bio-fuels as alternatives to traditional fossil fuels has attracted much attention recent years since bio-fuels belong to a family of renewable types of energy sources and do not contribute to the greenhouse effect. Traditional catalyst for this process suffers significant deactivation with time due to the presence of larger amounts of potassium in bio-fuels.

A possible solution of this problem is use of highly acidic supports which would interact with potassium stronger than active metal species [1, 2]. Among potential carriers, tungstated and sulfated zirconia are of high interest. Their acidic and textural properties can be modified by varying preparation conditions [3].

2 Catalyst Preparation

The preparation method involves two types: *coprecipitation* of tungsten and zirconia oxides with ammonium hydroxide (AH) [4], and *precipitation* with ethyl diamine (ED) [5], illustrated in the two following schemes, respectively:



The supports are both impregnated with vanadia to a concentration of 1.7-2 wt% vanadium. Poisoning with potassium is achieved by incipient wetness impregnation with KNO₃ to a K/V molar ratio at 0.2 and 0.4.

3 Support Characteristics


The supports were characterized through the X-ray diffraction, BET-area and ammonia-TPD. From the two latter, the concentration of acid sites can be calculated.

Sample	Calc Temp [°C]	BET [m ² /g]	Acid Conc. [μmol/m ²]	Crystallinity [%]	Phase Composition ^β [vol%]	
					tet-ZrO ₂	mon-ZrO ₂
WO ₃ /ZrO ₂ -AH	400	227	1.8	35.2	a ^α	a ^α
	500	167	2.3	37.1	a ^α	a ^α
	600	136	3.4	54.7	99.8	0.2
	700	100	3.8	64.9	76.8	23.1
	800	59	3.3	67.5	82.9	16.9
SO ₄ /ZrO ₂ -AH	700	85	3.0	76.1	51.4	48.6
SO ₄ /ZrO ₂ -ED	700	118	4.4	74.1	59.3	40.7

^α Amorphous.
^β Calculated with the Rietveld Refinement method. Normalized to the amount of crystalline zirconia.

Table 1: The WO₃/ZrO₂-AH and SO₄/ZrO₂-ED samples calcined at 700°C displayed highest concentration of acid sites to which ammonia could adsorb, with 3.8 μmol/m² and 4.4 μmol/m², respectively.

4 NO-SCR Activity



Reference catalyst: 3.0% V₂O₅ +7% WO₃/TiO₂ (anatase).
 All activities are normalized to the volume, where zirconia have a higher density than titania.

Fig. 1: Catalysts based on tungstated zirconia impregnated with vanadia, shows high activities in NO-SCR with ammonia, comparable with the activity of traditional catalyst (Ref). After alkali poisoning, K/V=0.2, catalysts based on tungstated zirconia calcined at 600°C and 700°C show the best resistance; deactivation at 350°C is only 36% and 28%, respectively, in comparison with 68% for the reference catalyst.




Fig 2: Catalysts based on sulfated supports display very high initial activities. After poisoning with potassium to K/V ratio 0.4, the reference catalyst has lost almost 80% of its initial activity at 350°C. For the tungstated catalyst with higher amount of potassium is also quite severe, 88%. The samples based on sulfated zirconia show best resistance towards poisoning with potassium, deactivation is 58% and 70% for the ED and AH samples, respectively.

5 Conclusions

Tungstated zirconia with high crystallinity shows good SCR properties and resistance towards alkali poisoning. The samples based on sulfated zirconia display very high initial SCR activities and show best resistance towards poisoning with potassium. Even though samples based on sulfated zirconia are much less affected by the poisoning with potassium, the deactivation is still quite severe indicating that potassium is eventually distributed between the acid sites of the support and active vanadia species.

References

- [1] A.L. Kustov, M.Yu. Kustova, R. Fehrmann, P. Simonsen, Appl. Catal. B, 58 (2005) 97-104
- [2] J. Due-Hansen, A.L. Kustov, S.B. Rasmussen, R. Fehrmann, C.H. Christensen, Appl. Catal. B, 66 (2006) 160-166
- [3] K. Arata, Appl. Catal. A, 146 (1996) 3-32
- [4] J.R. Sohn and M.Y. Park, Langmuir, 14 (1998) 6140-6145
- [5] L. D'Souza and A. Suchopar and K. Zhu, D. Baloyzova, M. Devadas, R. M. Richards, Microporous and Mesoporous Materials, 88 (2006) 22-30